



- ① FILTERED CONDENSER AIR INLET (Ambient Air In)
- ② CONDENSER OUTLET (Warm Ambient Air Out)
- ③ WARM AIR RETURN FROM ENCLOSURE
- ④ COOL AIR OUTLET TO ENCLOSURE

W2NA6C18DP53LV

by Wiegmann

Collection Name: Guardian X

Catalog ID: W2NA6C18DP53LV

Nema 4X Guardian X Series Air Conditioner, 53x22x13, 18,000 BTU/H, 23 V

Air conditioners are designed to perform under many harsh conditions and to provide the cooling and environmental protection that is required for sensitive electronic equipment.

- All models are UL/cUL listed
- Built-in condensate evaporator
- Closed-loop cooling
- Epoxy-coated evaporator and condenser coils
- Internal corrosion protection
- Programmable thermostat
- Reusable filter provided
- Zero ODP refrigerant

Product Details

General

Finish Type	Stainless Steel
Series	DP 53 Series (18,000 BTU/H)
Type	Air Conditioner
UPC	786725888238

Dimensions

Actual Depth	13 in
Actual Height	53 in
Actual Width	22 in
Weight	224 lb

Electrical Ratings

Hertz Input	60
Voltage Rating	230 V

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL • cUL
Nema Rating	4X