



- ① FILTERED CONDENSER AIR INLET (Ambient Air In)
- ② CONDENSER OUTLET (Warm Ambient Air Out)
- ③ WARM AIR RETURN FROM ENCLOSURE
- ④ COOL AIR OUTLET TO ENCLOSURE

## W2NA6C26DP60LV

by Wiegmann

Collection Name: Guardian X

Catalog ID: W2NA6C26DP60LV

Nema 4X Guardian X Series Air Conditioner, 60x24x13, 26,000 BTU/H, 230 V

Air conditioners are designed to perform under many harsh conditions and to provide the cooling and environmental protection that is required for sensitive electronic equipment.

- All models are UL/cUL listed
- Built-in condensate evaporator
- Closed-loop cooling
- Epoxy-coated evaporator and condenser coils
- Internal corrosion protection
- Programmable thermostat
- Reusable filter provided
- Zero ODP refrigerant

### Product Details

#### General

|             |                             |
|-------------|-----------------------------|
| Finish Type | Stainless Steel             |
| Series      | DP 60 Series (26,000 BTU/H) |
| Type        | Air Conditioner             |
| UPC         | 786725888252                |

#### Dimensions

|               |        |
|---------------|--------|
| Actual Depth  | 13 in  |
| Actual Height | 60 in  |
| Actual Width  | 24 in  |
| Weight        | 262 lb |

#### Electrical Ratings

|                |       |
|----------------|-------|
| Hertz Input    | 60    |
| Voltage Rating | 230 V |

#### Certifications and Compliance

|                  |   |
|------------------|---|
| Certified Listed | <ul style="list-style-type: none"> <li>• UL</li> <li>• cUL</li> </ul> |
| Nema Rating      | 4X  |