



- ① FILTERED CONDENSER AIR INLET (Ambient Air In)
- ② CONDENSER OUTLET (Warm Ambient Air Out)
- ③ WARM AIR RETURN FROM ENCLOSURE
- ④ COOL AIR OUTLET TO ENCLOSURE

W3NA4C3DP24L

by Wiegmann

Collection Name: Guardian

Catalog ID: W3NA4C3DP24L

Nema 4 Guardian Series Air Conditioner, 24x12x10, 3,000 BTU/H, 480 V

Air conditioners are designed to perform under many harsh conditions and to provide the cooling and environmental protection that is required for sensitive electronic equipment.

- All models are UL/cUL listed
- Built-in condensate evaporator
- Closed-loop cooling
- Epoxy-coated evaporator and condenser coils
- Internal corrosion protection
- Programmable thermostat
- Reusable filter provided
- Zero ODP refrigerant

Product Details

General

Color	Gray
Series	DP 24 Series (3,000 BTU/H)
Type	Air Conditioner
UPC	786725876037

Dimensions

Actual Depth	10 in
Actual Height	24 in
Actual Width	12 in
Weight	61 lb

Electrical Ratings

Amperage Rating	1.4
Hertz Input	60
Voltage Rating	480 V

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL • cUL
Nema Rating	4