



- ① FILTERED CONDENSER AIR INLET (Ambient Air In)
- ② CONDENSER OUTLET (Warm Ambient Air Out)
- ③ WARM AIR RETURN FROM ENCLOSURE
- ④ COOL AIR OUTLET TO ENCLOSURE

W3NA6C14DP50LV

by Wiegmann

Collection Name: Guardian X

Catalog ID: W3NA6C14DP50LV

Nema 4X Guardian X Series Air Conditioner, 50x20x12, 14,000 BTU/H, 480 V

Air conditioners are designed to perform under many harsh conditions and to provide the cooling and environmental protection that is required for sensitive electronic equipment.

- All models are UL/cUL listed
- Built-in condensate evaporator
- Closed-loop cooling
- Epoxy-coated evaporator and condenser coils
- Internal corrosion protection
- Programmable thermostat
- Reusable filter provided
- Zero ODP refrigerant

Product Details

General

Finish Type	Stainless Steel
Series	DP 50 Series (14,000 BTU/H)
Type	Air Conditioner
UPC	786725876020

Dimensions

Actual Depth	12 in
Actual Height	50 in
Actual Width	20 in
Weight	207 lb

Electrical Ratings

Hertz Input	60
Voltage Rating	480 V

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"> • UL • cUL
Nema Rating	4X