



WA080804GSCG

by Wiegmann
Catalog ID: WA080804GSCG

N4 Gasketed Screw-Cover 8X8X4 Carbon Steel - Galvanized

- Bodies and covers fabricated from 14 gauge G-90 grade galvanized steel. Seams are continuously welded and ground smooth. Cover contains closed cell oil resistant neoprene gasket. Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc from entering into the box through the screw holes. Ground stud located in door. No holes, knockout, or rear mounting holes.

Product Details

General

Application	Designed for use as wiring box, junction box, pull box, and terminal box in many indoor or outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Galvanized
Listings	UL
Material	Carbon Steel
Mounting Method	Mounting Holes
Type	Enclosure
UPC	786725310166

Dimensions

Actual Depth	4.45 in
Actual Height	4.450 in
Cubic Capacity	144 cu.in
Depth	4 in
Height	4 in
Weight	6 lb
Width	9 in

Certifications and Compliance

Certified Listed	UL
Nema Rating	4
UL Listed	Yes

