



WA363612GSCG

by Wiegmann
Catalog ID: WA363612GSCG

N4 Gasketed Screw-Cover 36X36X12 Carbon Steel - Galvanized

- Bodies and covers fabricated from 12 gauge G-90 grade galvanized steel. Seams are continuously welded and ground smooth. Cover contains closed cell oil resistant neoprene gasket. Enclosure comes with stainless steel cover screws which thread into sealed wells to prevent liquid, dust, etc from entering into the box through the screw holes. Ground stud located in door. No holes, knockout, or rear mounting holes.

Product Details

General

Application	Designed for use as wiring box, junction box, pull box, and terminal box in many indoor or outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Galvanized
Listings	UL
Material	Carbon Steel
Mounting Method	Mounting Holes
Type	Enclosure
UPC	786725848904

Dimensions

Cubic Capacity	7448 cu.in
Depth	14 in
Height	14 in
Weight	110 lb
Width	38 in

Certifications and Compliance

Certified Listed	UL
Nema Rating	4

UL Listed	Yes
-----------	-----