

WA60X6112SSN4

by Wiegmann

Catalog ID: WA60X6112SSN4

N4X Two Door Floor-Mount Right Flanged Disconnect 60X61X12 304
Stainless Steel



Product Details

General

Application	Enclosures having the "WM" preferred cutout are sized for use with up to 200A disconnect switches and up to 400A circuit breakers unless otherwise specified. The "WM" preferred cutout accepts the smaller operating handle whose mounting hole centers are 4.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	3-Point Padlocking Handle
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Method	15 in. floor stands
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725869626

Dimensions

Actual Depth	12.12 in
Actual Height	60.120 in
Actual Width	61.750 in
Cubic Capacity	44640 cu.in
Depth	12 in
Height	60 in

Weight	535 lb
Width	62 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4X
UL Listed	Yes