



* Representative image

WA6AXFN

by Wiegmann

Catalog ID: WA6AXFN

Prop65_Cancer&Reproductive

Axial Fan - 115V / 240CFM 6 in.

- Fan furnished standard with 24 inch lead wire, 90 degree plug attached
- Impeller and frame are glass reinforced thermoplastic, UL94-VO
- Rated Speed (RPM) 2800/3500
- Noise Level 46 +/- 2
- Maximum Air Flow (M3/MIN) 5.4/6.6
- Maximum Air Flow (CFM) 190/235
- Maximum Static Pressure/H2O 5.4/6.6

Product Details

General

Application	Designed for use in enclosures where space is limited and reliable cooling is required.
Color	Black
Input	26/35 Watts
Material	Die Cast Aluminum
Type	Axial Fan
UPC	786725602803

Dimensions

Depth	2 in
Height	6.77 in
Weight	2.5 lb
Width	6.77 in

Electrical Ratings

Frequency Rating	50/60 Hz
Voltage Rating	115 V

Logistics

Carton Quantity	1
-----------------	---