



WA72XM2718SSN4

by Wiegmann
Catalog ID: WA72XM2718SSN4

N4X Single Door Right Flanged Disconnect 72X27X18 304 Stainless Steel

Product Details

General

Application	Enclosures having the "WM" preferred cutout are sized for use with up to 200A disconnect switches and up to 400A circuit breakers unless otherwise specified. The "WM" preferred cutout accepts the smaller operating handle whose mounting hole centers are 4.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	3-Point Padlocking Handle
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725869732

Dimensions

Actual Depth	18.12 in
Actual Height	72.120 in
Actual Width	27.500 in

Cubic Capacity	36288 cu.in
Depth	18 in
Height	72 in
Weight	368 lb
Width	28 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	4X
UL Listed	Yes