



## WA72XM7724SSN4

by Wiegmann  
Catalog ID: WA72XM7724SSN4

N4X Double Door Right Flanged Disconnect 72X77X24 304 Stainless Steel

### Product Details

#### General

Application	Enclosures having the "WM" preferred cutout are sized for use with up to 200A disconnect switches and up to 400A circuit breakers unless otherwise specified. The "WM" preferred cutout accepts the smaller operating handle whose mounting hole centers are 4.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	3-Point Padlocking Handle
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725869848

#### Dimensions

Actual Depth	24.12 in
Actual Height	72.120 in
Actual Width	77.750 in

Cubic Capacity	134784 cu.in
Depth	24 in
Height	72 in
Weight	895 lb
Width	78 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	4X
UL Listed	Yes