



## WA84XM7718SSN4

by Wiegmann  
Catalog ID: WA84XM7718SSN4

N4X Double Door Right Flanged Disconnect 84X77X18 304 Stainless Steel

### Product Details

#### General

Application	Enclosures having the "WM" preferred cutout are sized for use with up to 200A disconnect switches and up to 400A circuit breakers unless otherwise specified. The "WM" preferred cutout accepts the smaller operating handle whose mounting hole centers are 4.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	3-Point Padlocking Handle
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	2
Type	Enclosure
UPC	786725869855

#### Dimensions

Actual Depth	18.12 in
Actual Height	84.120 in
Actual Width	77.750 in

Cubic Capacity	117936 cu.in
Depth	18 in
Height	84 in
Weight	1200 lb
Width	78 in

#### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	4X
UL Listed	Yes