



WADW231302

by Wiegmann
Catalog ID: WADW231302

NEMA 4 Deep Hinged Window 22.8X13.5X2.8 Carbon Steel-Gray

The Wiegmann Universal Deep Hinged Door Kit is styled after Wiegmann's N412 Ultimate Series enclosures. Kits are compatible with any NEMA 3R, 4, 4X, and 12 rated enclosures.

- Quarter-turn style latching for easy access
- Poured in place gasket
- Removable concealed hinge
- Drill template included for ease of mounting and guaranteed alignment
- Polycarbonate window for clear visibility

Product Details

General

Accessory Type	Window/Door Kit
Color	Gray
Finish Type	Polyester Powder
Latches Type	Quarter Turn Latch
Material	Carbon Steel
Type	Accessory
UPC	786725876723

Dimensions

Actual Depth	2.75 in
Actual Height	22.75 in
Actual Width	13.5 in
Depth	2 in
Height	23 in
Weight	17 lb
Width	13 in

Certifications and Compliance

Certified Listed	UL Recognized 508A
Nema Rating	4, 12

