



WC1460T

by Wiegmann
Catalog ID: WC1460T

Top For WC1460BD Carbon Steel - Gray

Designed to hold electrical and electronic controls and instruments. Pushbuttons, pilot lights, meters, switches etc., can be mounted on the instrument panel. Interior components are motorized on stationary sub panels, swing-out sub panels or relay rack angles (panels are optional). Heavy duty construction provides protection from dirt, dust, oil and water. Numerous accessories and variable combinations make these consoles most versatile.

- Fabricated from 14 gauge steel. Top unit is 12.5" deep to accommodate most instruments. Seams are continuously welded and ground smooth, less knockouts or holes. Instrument and access panels have captivated screws which thread into sealed wells. 4 holes are provided in bottom of top for mounting to body. Instrument and access panels are removable. Closed cell neoprene gasket.

Product Details

General

Application	For use with WC1460BD console.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Screw
Finish Type	Polyester Powder
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Series	WC14
Type	Console Top
UPC	786725444656

Dimensions

Actual Depth	16.13 in
Actual Height	12.630 in
Actual Width	60.13 in
Depth	16 in
Height	13 in
Weight	96 lb
Width	60 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 12
UL Listed	Yes