



WC16C36

by Wiegmann
Catalog ID: WC16C36

N12 Operator Interface Consolelet 16X36 Carbon Steel - Gray

Designed to house a variety of electronic control or instrumentation devices. Consolelets provide protection from dust, dirt, oil, and water. Flexible design allows for mounting on either or two sides, creating control surfaces of 30 degrees or 60 degrees. Consolelets can be mounted on desktops, pedestal or other flat surfaces.

- Fabricated from carbon steel
- Seams are continuously welded and ground smooth
- Grounding provisions

Bodies and doors fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Captive cover screws thread into sealed wells. Control panel is continuously hinged along bottom edge. Closed cell oil resistant neoprene gasket. Grounding provisions included.

Product Details

General

| | |
|--------------|--|
| Application | Designed to house a variety of electronic control or instrumentation devices. Consolelets provide protection from dust, dirt, oil, and water. Flexible design allows for mounting on either of two sides, creating control surfaces of 30 degrees or 60 degrees. |
| Color | Gray |
| Construction | Continuously Welded Seams |
| Cover Type | Screw |
| Finish Type | Polyester Powder |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Series | WC-C |
| Type | Consolelets |

| | |
|-----|--------------|
| UPC | 786725441600 |
|-----|--------------|

Dimensions

| | |
|--------------|----------|
| Actual Depth | 11.09 in |
| Depth | 11 in |
| Height | 16 in |
| Weight | 47 lb |
| Width | 36 in |

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | NEMA 12 |
| UL Listed | Yes |