



Wiring Device-Kellems

Wire Management, Hose Containment Grips, Double Eye Grip, 24" Mesh Length, Cable Dia: 0.50 in-0.94 in



By Hubbell Wiring Device-Kellems
Catalog # [014021224](#)

Wire Management, Hose Containment Grips, Double Eye Grip, 24" Mesh Length, Cable Dia: 0.50 in-0.94 in

Features

- These grips will prevent serious injury to personnel and damage to equipment by holding the hose in place in the event of hose failure
- Kellems® patented Hose Containment Grips are made of stainless steel double weave mesh construction for high strength and come complete with hose clamps

Application

Used where fastening is made with eyebolts or similar anchor terminations

General

Approx Breaking Strength	4,250 lbs
Item Type	Double Eye Grip (Type E)
Material	Stainless Steel
UPC	783585437903

Conductor Related

Cable Diameter Range	0.50 in-0.94 in
----------------------	-----------------

Product Assets

- [Catalog Page - Wiring X-46 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Pulp & Paper Solutions](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Kellems Wire Management Solutions](#)
- [Video - Kellems Wire Management Solutions](#)

Related Products

- [014021223 - Wire Management, Hose Containment Grips, Double Eye Grip, 24" Mesh Length, Cable Dia: 0.75 in-1.25 in](#)
- [014021138 - Wire Management, Hose Containment Grips, Universal Bale Grip, 24" Mesh Length, Cable Dia:0.50 in-0.94 in](#)
- [014021152 - Wire Management, Hose Containment Grips, Tube Grips, Type T, 24" Mesh Length, Cable Dia: 0.50 in-0.94 in](#)
- [014021156 - Wire Management, Hose Containment Grips, Split Fitting, 24" Mesh Length, Cable Dia:0.50 in-0.94 in](#)
- [014021139 - Wire Management, Hose Containment Grips, Universal Bale Grip, 24" Mesh Length, Cable Dia:0.50 in-0.94 in](#)



A proud member of the Hubbell Family.