



Audio/Video Connector, D-Sub, 15-Pin, Female 8-Pin, 90 Degree, Single Pack

By Hubbell Wiring Device-Kellems
Catalog # [15A6PI](#)



Audio/Video Connector, D-Sub, 15-Pin, Female 8-Pin, 90 Degree, Single Pack

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	X-END AV Plug-n-Play System
Material - Mounting Hardware	Snap-On- Snap-Fit
Temperature Rating	Per TIA
Type	VGA
UPC	662620290898

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-15A6PI-SPEC-EN | REV 5/2023