



## Audio/Video Connector, D-Sub, 15-Pin, Female 8-Pin to Female, 180 Degree, 10 Pack

By Hubbell Wiring Device-Kellems  
Catalog # [15S6P10](#)



Audio/Video Connector, D-Sub, 15-Pin, Female 8-Pin to Female, 180 Degree, 10 Pack

### Application

15 Pin to 8 Pin Connector, Straight 180

### General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	X-END AV Plug-n-Play System
Material - Mounting Hardware	Snap-On- Snap-Fit
Temperature Rating	Per TIA
Type	VGA
UPC	662620286679

### Dimensions

Display Size Standard Sized Product

### Electrical Ratings

Connectivity	Plug-N-Play
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

### Logistics

Carton Quantity 50

### Product Assets

[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-15S6P10-SPEC-EN | REV 5/2023