



Straight Blade Devices, Tamper Resistant Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 15A 125V, 5-15R

By Hubbell Wiring Device-Kellems
 Catalog # [2172GYLTRA](#)



Straight Blade Devices, Tamper Resistant Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant decorator face
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

General

Color	Gray
Horsepower - Maximum	0.5
Indicator(s) Type	Green LED
Item Type	Style Line Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - Wiring A-22 Catalog page](#)
- [Catalog Page - Wiring M9 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Installation Manuals - WIRING_PD2504_INSTALLINST](#)
- [Literature - Tamper-Resistant Receptacles for Healthcare](#)
- [Literature - WLBD026_Duct Products Brochure_WEB](#)
- [Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
- [Literature - Hubbell-Pro Hospital Grade Receptacles](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Tamper-Resistant Receptacles](#)

Related Products

Accommodation - #14-#10
AWG copper stranded or
solid conductor only

- Mechanical - Terminal
Identification - Terminals
identified in accordance
with UL 498 and CSA

Series Hubbell-Pro
Style Style Line decorator
Type Duplex Receptacle
UPC 783585541785

Dimensions

Dimensions 3.28 in x 1.57 in x 1.15 in
Height 1.15 in
Length 3.28 in
Weight 0.2 lb
Width 1.57 in

2172REDLTRA - Straight Blade Devices, Tamper Resistant
Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro,
LED Indicator, 15A 125V, 5-15R

2172LTRA - Straight Blade Devices, Tamper Resistant
Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro,
LED Indicator, 15A 125V, 5-15R

HBL8200SGGYA - Straight Blade Devices, Receptacles,
Duplex, Tamper Resistant Hospital Grade, 2-Pole 3-Wire
Grounding, 15A 125V, 5-15R, Gray, Single Pack

2172GYL - Straight Blade Devices, Decorator Duplex
Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 15A
125V, 2-Pole 3-Wire Grounding, 5-15R, Gray

HBL8215CAT - Straight Blade Devices, Male Plug, Insulgrip,
Hospital Grade, Angled, 2-Pole 3-Wire Grounding, 15A 125V, 5-
15P, Transparent, Single Pack



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-2172GYLTRA-SPEC-EN | REV 5/2023