

Straight Blade Devices, Tamper
Resistant Decorator Duplex
Receptacle, Hospital Grade,
Hubbell-Pro, 15A 125V, 2-Pole 3-
Wire Grounding, 5-15R, Brown

By Hubbell Wiring Device-Kellems
Catalog # [2172TRA](#)

Straight Blade Devices, Tamper Resistant Decorator Duplex
Receptacle, Hospital Grade, Hubbell-Pro, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Brown

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant decorator face
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

General

Catalog Number	2172TRA
Color	Brown
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	0.5
Item Type	Style Line Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hubbell-Pro



Style	Style Line decorator
Type	Duplex Receptacle
UPC	783585541877

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Certified to CSA, C22.2, No. 42 File 285• Fed. Spec. W-C-596• NEMA® WD-6 Compliant• UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Product Assets

[Catalog Page - WDK L-9 Catalog Page](#)

[Catalog Page - WDK A-27 Catalog Page](#)

[Catalogs - WDK Catalog Full 2024](#)

[Installation Manuals - WIRING_PD2504_INSTALLINST](#)

[Literature - Tamper-Resistant Receptacles for Healthcare](#)

[Literature - Heavy Duty Tamper-Resistant Receptacles](#)

[Literature - Duct Products Guide](#)

[Literature - Tamper-Resistant Receptacles](#)

[Literature - Hubbell-Pro Hospital Grade Receptacles](#)

[Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)

[Specifications - 2172TRA](#)

[Warranty - Industrial & Commercial Products](#)

[Video - Tamper-Resistant Receptacles](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-2172TRA-SPEC-EN | REV 3/2025