

# Straight Blade Devices, Tamper Resistant Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 20A 125V, 5-20R

By Hubbell Wiring Device-Kellems  
Catalog # [2182GYLTRA](#)

Straight Blade Devices, Tamper Resistant Decorator Duplex Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Gray



## Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant decorator face
- Steel mounting strap

## Application

Hubbell-Pro Heavy Duty Hospital Grade

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	2182GYLTRA
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Horsepower - Maximum	1
Indicator(s) Type	Green LED
Item Type	Style Line Decorator Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact

Series	Hubbell-Pro
Style	Style Line decorator
Type	Duplex Receptacle
UPC	783585541945

## Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	2500 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#12 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• Certified to CSA, C22.2, No. 42 File 285</li><li>• Fed. Spec. W-C-596</li><li>• NEMA® WD-6 Compliant</li><li>• UL Listed to UL498 File No. E2186</li></ul>
Nema Rating	5-20R

## Logistics

Carton Quantity 10

## Product Assets

[Catalog Page - WDK L-9 Catalog Page](#)  
[Catalog Page - WDK A-27 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)

[Installation Manuals - WIRING\\_PD2504\\_INSTALLINST](#)  
[Literature - Tamper-Resistant Receptacles for Healthcare](#)  
[Literature - Duct Products Guide](#)  
[Literature - Hubbell-Pro Hospital Grade Receptacles](#)  
[Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)  
[Specifications - 2182GYLTRA](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - Tamper-Resistant Receptacles](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK-2182GYLTRA-SPEC-EN | REV 10/2024