

HUBBELL
Wiring Device-Kellems

**Straight Blade Devices, Tamper
Resistant Decorator Duplex
Receptacle, Hospital Grade,
Hubbell-Pro, LED Indicator, 20A
125V, 5-20R**

By Hubbell Wiring Device-Kellems
Catalog # [2182WLTRA](#)

Straight Blade Devices, Tamper Resistant Decorator Duplex
Receptacle, Hospital Grade, Hubbell-Pro, LED Indicator, 20A
125V, 2-Pole 3-Wire Grounding, 5-20R, White



Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant decorator face
- Steel mounting strap

General

| | |
|------------------------------|--|
| Application | Hubbell-Pro Heavy Duty Hospital Grade |
| Catalog Number | 2182WLTRA |
| Color | White |
| EU RoHS Indicator | Contact Manufacturer |
| Horsepower - Maximum | 1 |
| Indicator(s) Type | Green LED |
| Item Type | Style Line Decorator Duplex |
| Material | Nylon |
| Material - Mounting Hardware | Screw Mounting |
| Number Of Poles | 2-Pole |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Operating Temperature | Maximum continuous 75°C and minimum -40°C without Impact |
| Performance | Electrical - Current Interrupting - Certified for current interrupting at full rated current Electrical - Dielectric Voltage - Withstands 2,000V minimum Environmental - Flammability - UL 94V-2 Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact) Mechanical - Product Identification - Ratings are a permanent part of the device Mechanical - Terminal Accommodation - #12-#10 AWG stranded or solid copper wire only Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA |
| Series | Hubbell-Pro |
| Style | Style Line decorator |
| Type | Duplex Receptacle |
| UPC | 783585542041 |

Dimensions

| | |
|------------|-----------------------------|
| Dimensions | 3.28 in x 1.57 in x 1.15 in |
| Height | 1.15 in |
| Length | 3.28 in |
| Weight | 0.2 lb |
| Width | 1.57 in |

Electrical Ratings

| | |
|----------------------------|-------------------------------------|
| Amperage Rating | 20 A |
| Connectivity | Back and Side Wired Screw Terminals |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Phase | Single Phase |
| Voltage Rating | 125 VAC |
| Voltage Rating Description | 125 V |
| Wattage | 2500 W |

Conductor Related

| | |
|-----------------|--------------------|
| Number Of Wires | 3-Wire |
| Wire Size | #12 AWG to #10 AWG |

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | Certified to CSA, C22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant UL Listed to UL498 File No. E2186 |
| Nema Rating | 5-20R |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

[Catalog Page - WDK A-27 Catalog Page](#)
[Catalog Page - WDK L-9 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - Tamper-Resistant Receptacles for Healthcare](#)
[Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
[Literature - Duct Products Guide](#)
[Literature - Hubbell-Pro Hospital Grade Receptacles](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Tamper-Resistant Receptacles](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK-2182WLTRA-SPEC-EN | REV 6/2024