



CFB2G & CFB4G Rectangular Furniture Feed Series, Surface Cover Assembly, Satin Nickel Powder Paint Finish

By Hubbell Wiring Device-Kellems
Catalog # [24GCFFCVRNK](#)



Concrete Floors, Recessed, CFB2G & CFB4G Rectangular Furniture Feed Series, Surface Cover Assembly, Satin Nickel Powder Paint Finish

Features

- Surface Style Cover
- (1) 2" Conduit Hub and (1) 3/4" Conduit Hub
- Die Cast Aluminum Cover Construction for Enhanced Durability
- Meets UL 514A Scrub Water Requirements
- ADA Compliant

Application

For Use with Concrete Floor Boxes

General

Application - For Use On	Concrete
Color	Nickel Powder Coat
Construction	Cast
Construction Material - Main	Metallic
Cover Shape	Rectangle
Cover Type	Rectangle
EU RoHS Indicator	Contact Manufacturer
Finish Type	Nickel
Material	Cast Aluminum
Mounting Method	Mounts to Box
Mounting Type	(4) Screw Mount
Number of Gang(s)	2-Gang
Series	Recessed - CFB Series
Size	Standard Sized Product
Sub Brand	Recessed Concrete Floor Boxes
Type	Furniture Feed Concrete Floor Box Cover
Type of Use	Carpet/Surface
Typical Application	Carpet/Surface
UPC	783585446578

Dimensions

Length	11.69 in
Width	7.19 in

Conductor Related

Cable Entry	(2) Threaded Hubs
-------------	-------------------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">• cULus• UL514
----------------------	---

Product Assets

- [Catalog Page - Wiring P-6 Catalog page](#)
- [Catalog Page - Wiring P-7 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - 24GCFFCVRNK AutoCAD Drawing](#)
- [Engineering Drawing - 2G RECESSED FLOOR BOX Drawing](#)
- [Engineering Drawing - 4 Gang Recessed Floor Box Drawing](#)
- [Installation Manuals - WIRING_PD2746_INSTALLINST](#)
- [Sales Drawings - WDK_24GCFFCVR_DRAWING_PDF](#)
- [Sales Drawings - WDK_CFB2G_DRAWING_PDF](#)
- [Sales Drawings - WDK_CFB4G_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - SystemOne Recessed Floor Boxes](#)

Related Products

- [CFB2G25CR - 2-Gang CFB Series Box for Rectangular Covers, 2.50" Minimum Depth of Pour, Corrosion Resistant Paint](#)
- [CFB4G25CR - 4-Gang CFB Series Box for Rectangular Covers, 2.50" Minimum Depth of Pour, Corrosion Resistant Paint](#)
- [CFB2G30CR - 2-Gang CFB Series Box for Rectangular Covers, 3.00" Minimum Depth of Pour, Corrosion Resistant Paint](#)
- [CFB4G25 - 4-Gang CFB Series Box for Rectangular Covers, 2.50" Minimum Depth of Pour](#)
- [CFB4G30CR - 4-Gang CFB Series Box for Round Covers, 3.75" Minimum Depth of Pour](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-24GCFFCVRNK-SPEC-EN | REV 5/2023