

Straight Blade Devices,  
Receptacles, Duplex,  
Commercial/Industrial Grade, 2-  
Pole 3-Wire Grounding, 15A 125V, 5-  
15R, Blue

By Hubbell Wiring Device-Kellems  
Catalog # 5262BL



Straight Blade Devices, Receptacles, Duplex,  
Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 15A  
125V, 5-15R, Blue

Application

Hubbell-Pro Extra Heavy Duty

General

Catalog Number	5262BL
Color	Blue
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry unless protected by additional means
Item Type	Traditional Duplex
Material	Thermoplastic/Composite
Material - Mounting Hardware	Screw Mounting
Mounting Type	Screw Mount
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Finder Groove Face
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Standard Duplex
UPC	783585147178

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
-----------------	------

Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications And Compliance

Industry Standard(s)	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- Catalog Page - [WDK A-28 Catalog Page](#)
- Catalogs - [WDK Catalog Full 2024](#)
- Engineering Drawing - [M10822\\_ACAD](#)
- Installation Manuals - [WIRING\\_PD2504\\_INSTALLINST](#)
- Sales Drawings - [M10822](#)
- Specifications - [5262BL](#)
- Warranty - [Industrial & Commercial Products](#)