



Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, Black

By Hubbell Wiring Device-Kellems
Catalog # [5462BK](#)



Straight Blade Devices, Receptacles, Duplex, Heavy Duty
Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, Black

Features

- Back and side wired
- Fed- Spec UL listed
- Smooth nylon face, Brass triple-wipe contacts

Application

Hubbell-Pro Heavy Duty

General

Color	Black
Horsepower - Maximum	2
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94 V-2 • Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only • Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series

Hubbell-PRO

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating Description	250 V
Wattage	5000 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA 22.2, No. 42 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	--

Nema Rating	6-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring A-23 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - 5462BK AutoCAD Drawing](#)
[Literature - Hubbell-PRO 15A & 20A 250V Duplex Receptacles](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[HBL5466CA - Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 250V, 6-20P and White](#)

[HBL5462BK - Straight Blade Devices, Receptacles, Duplex, Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, Black, Single Pack](#)

[IG5462 - Straight Blade Devices, Receptacles, Duplex, Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-20R, Orange, Single Pack](#)

[IG5662 - Straight Blade Devices, Receptacles, Duplex, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-](#)

Style	Smooth Face	Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Orange, Single Pack
Type	Standard Duplex	
UPC	78358555935	5662BK - Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Black

Dimensions

Weight	0.2 lb
--------	--------



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-5462BK-SPEC-EN | REV 5/2023