



# Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [5662GY](#)



Straight Blade Devices, Receptacles, Duplex, Heavy Duty  
Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Gray

## Features

- Back and side wired
- Fed- Spec UL listed
- Smooth nylon face, Brass triple-wipe contacts

## Application

Hubbell-Pro Heavy Duty

## General

Color	Gray
Horsepower - Maximum	1.5
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94 V-2</li> <li>• Environmental - Operating Temperatures - Maximum continuous 75°C, minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> <li>• Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only</li> <li>• Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA</li> </ul>

Series

Hubbell-PRO

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating Description	250 V
Wattage	3750 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA 22.2, No. 42</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul>
----------------------	--

Nema Rating	6-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalog Page - Wiring A-23 Catalog page](#)  
[Catalogs - Wiring Full Catalog](#)  
[Engineering Drawing - 5662GY AutoCAD Drawing](#)  
[Literature - Hubbell-PRO 15A & 20A 250V Duplex Receptacles](#)  
[Warranty - Industrial & Commercial Products](#)

## Related Products

[5662GY - Straight Blade Devices, Receptacles, Duplex, Heavy Duty Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Gray](#)  
[HBL5666C - Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 15A 250V, 6-15P and White](#)  
[HBL5666CA - Straight Blade Devices, Male Plug, Insulgrip Heavy Duty, Industrial/Commercial Grade, Angled, 2-Pole 3- Wire Grounding, 15A 250V, 6-15P and White](#)  
[IG5662 - Straight Blade Devices, Receptacles, Duplex, Specification Grade, 2-Pole 3-Wire Grounding, 15A 250V, 6-15R, Orange, Single Pack](#)

Style  
Type  
UPC

Smooth Face  
Standard Duplex  
783585555799

15R, Orange, Single Pack  
IG5462 - Straight Blade Devices, Receptacles, Duplex,  
Specification Grade, 2-Pole 3-Wire Grounding, 20A 250V, 6-  
20R, Orange, Single Pack

## Dimensions

Weight 0.2 lb



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-5662GY-SPEC-EN | REV 5/2023