



# Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black

By Hubbell Wiring Device-Kellems  
 Catalog # [8200BKTRA](#)



Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black

## Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

## Application

Hubbell-Pro Heavy Duty Hospital Grade

## General

Color	Black
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> <li>• Electrical - Current Interrupting - Certified for current interrupting at full rated current</li> <li>• Electrical - Dielectric Voltage - Withstands 2,000V minimum</li> <li>• Environmental - Flammability - UL 94V-2</li> <li>• Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact)</li> <li>• Mechanical - Product Identification - Ratings are a permanent part of the device</li> <li>• Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or</li> </ul>

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• Certified to CSA, C22.2, No. 42 File 285</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul>
----------------------	---

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

- [Catalog Page - Wiring A-22 Catalog page](#)
- [Catalog Page - Wiring M8 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Literature - Tamper-Resistant Receptacles for Healthcare](#)
- [Literature - WLBD026\\_Duct Products Brochure\\_WEB](#)
- [Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
- [Literature - Heavy Duty Tamper-Resistant Receptacles](#)
- [Literature - Tamper-Resistant Receptacles](#)
- [Literature - Hubbell-Pro Hospital Grade Receptacles](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Tamper-Resistant Receptacles](#)

## Related Products

AWG copper stranded or solid conductor only

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series Hubbell-Pro  
Style Smooth Face  
Type Receptacle  
UPC 783585542096

### Dimensions

Dimensions 3.28 in x 1.57 in x 1.15 in  
Height 1.15 in  
Length 3.28 in  
Weight 0.2 lb  
Width 1.57 in

8200BKLTRA - Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R

8200BKL - Straight Blade Devices, Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black.

8200BK - Straight Blade Devices, Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black

HBL8200BK - Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole 3-Wire Grounding, 15A, 125V, 5-15R, Black, Single Pack

8200GYTRA - Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-8200BKTRA-SPEC-EN | REV 5/2023