



Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Red

By Hubbell Wiring Device-Kellems
 Catalog # [8200REDTRA](#)



Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Red

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

General

Color	Red
Horsepower - Maximum	0.5
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device • Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
----------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - Wiring A-22 Catalog page](#)
- [Catalog Page - Wiring M8 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Literature - Tamper-Resistant Receptacles for Healthcare](#)
- [Literature - WLBD026_Duct Products Brochure_WEB](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
- [Literature - Heavy Duty Tamper-Resistant Receptacles](#)
- [Literature - Hubbell-Pro Hospital Grade Receptacles](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Tamper-Resistant Receptacles](#)

Related Products

AWG copper stranded or solid conductor only

- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

Series Hubbell-Pro
Style Smooth Face
Type Receptacle
UPC 783585542195

Dimensions

Dimensions 3.28 in x 1.57 in x 1.15 in
Height 1.15 in
Length 3.28 in
Weight 0.2 lb
Width 1.57 in

HBL8200RMRI - Straight Blade Devices, Receptacles, Duplex, Hospital Grade, MRI Series, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Red

8200RED - Straight Blade Devices, Duplex Receptacle, Hospital Grade, Hubbell-Pro, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Red

HBL8215C - Straight Blade Devices, Male Plug, Insulgrip, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Black and White, Single Pack

8200BKTRA - Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Black

8200TRA - Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-8200REDTRA-SPEC-EN | REV 5/2023