



Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R

By Hubbell Wiring Device-Kellems
Catalog # [8200WLTRA](#)



Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White

Features

- Tamper-resistant shutter complies with national electrical code requirements
- Green LED Power Indicators to identify emergency circuits
- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Application

Hubbell-Pro Heavy Duty Hospital Grade

General

Color	White
Horsepower - Maximum	0.5
Indicator(s) Type	Green LED
Item Type	Traditional Duplex
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device

Electrical Ratings

Amperage Rating	15 A
Connectivity	Back and Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 V
Wattage	1875 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"> • Certified to CSA, C22.2, No. 42 File 285 • Fed. Spec. W-C-596 • NEMA® WD-6 Compliant • UL Listed to UL498 File No. E2186
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - Wiring A-22 Catalog page](#)
- [Catalog Page - Wiring M8 Catalog page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Literature - Tamper-Resistant Receptacles for Healthcare](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - WLBD026_Duct Products Brochure_WEB](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - Hubbell-PRO Hospital Grade TR Receptacles](#)
- [Literature - Hubbell-Pro Hospital Grade Receptacles](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Tamper-Resistant Receptacles](#)

Related Products

Related Products

- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

HBL8215C - Straight Blade Devices, Male Plug, Insulgrip, Hospital Grade, Straight, 2-Pole 3-Wire Grounding, 15A 125V, 5-15P, Black and White, Single Pack

8200GYLTRA - Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, Gray

8200IVLTRA - Straight Blade Devices, Tamper Resistant, Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R

HBL8200HW - Straight Blade Devices, Receptacles, Duplex, Compact Hospital Grade, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R, White, Bulk Packed

8200BKLTRA - Straight Blade Devices, Tamper Resistant Duplex Receptacle, Hubbell-Pro, Hospital Grade, LED Indicator, 2-Pole 3-Wire Grounding, 15A 125V, 5-15R

Series	Hubbell-Pro
Style	Smooth Face
Type	Receptacle
UPC	783585542218

Dimensions

Dimensions	3.28 in x 1.57 in x 1.15 in
Height	1.15 in
Length	3.28 in
Weight	0.2 lb
Width	1.57 in



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-8200WLTRA-SPEC-EN | REV 5/2023