



Adapters, NEMA 5-15P to 15A NON-NEMA Locking

By Hubbell Wiring Device-Kellems
Catalog # [9054A](#)



Adapters, NEMA 5-15P to 15A NON-NEMA Locking

Application

Heavy Duty

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Plug-In Adapter
Material	Thermoplastic
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585779508

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Plug-In
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring_Catalog_CC4_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[HBL5273L - Locking Devices, Twist-Lock®, Accessories, Adapters, 15A 125V, 3-Wire Plug in 2-Wire Receptacle, 2-15-5-15R, White](#)
[9053A - Adapters, 15A Non-NEMA Locking to NEMA 5- 15R, White](#)
[HBL5289 - Plug In Adapter, 15A 125V Crow Foot to 5- 15R](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-9054A-SPEC-EN | REV 5/2023