

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Receptacle and Inlet Angle Adapter, For 20A and 30A Mounting Screws Included

By Hubbell Wiring Device-Kellems
Catalog # [AA2030PS](#)

Heavy Duty Product, IEC Pin and Sleeve Devices, Industrial Grade, Accessory, Receptacle and Inlet Angle Adapter, 20A and 30A Mounting Screws Included, Gray Cast Aluminum

Features

- Industrial Grade
- Receptacle and Inlet Angle Adapter
- For 20A and 30A Mounting Screws Included

Application

Non-Metallic

General

Catalog Number	AA2030PS
Color	Gray
Construction	Fabricated
EU RoHS Indicator	No
Item Type	Mounting Box
Knockouts	None
Material	Composite
Material - Mounting Hardware	Mounting Screws
Number Of Outlets	Accepts 1-Device
OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	Accessory Item - Angle Adapter
Style	For 20 And 30A Watertight Safety Shroud Receptacles And Inlets
Temperature Range	Limited By Device
Type	Back Box
UPC	783585882215

Dimensions



Dimensions	4.25 in x 4.76 in x 3.62 in
Display Size	For 16, 20, 30 and 32 Amp Devices
Height	3.62 in
Length	4.25 in
Weight	1.85 lb
Width	4.76 in

Certifications And Compliance

Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	1
Pallet Quantity	100

Product Assets

- [Catalog Page - WDK G-28](#)
- [Catalog Page - WDK B-54](#)
- [Catalog Page - WDK C-4](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - AA2030PS AutoCAD Drawing](#)
- [Installation Manuals - WIRING_AA2030PS_INSTALLINST](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_AA2030PS_DRAWING_PDF](#)
- [Specifications - Wiring AA2030PS Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)