



Single-Gang Keystone Wallplate, Angled, 4-Port, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [AFP14E](#)

Hubbell Premise Wiring's angled wall plates offer 45° jack and Audio/Video connector mounting along with TIA/EIA-606A station labeling ability and the traditional features of HPW's standard flush wall plates. The design of the AFP plate positions the patch cord down at an angle of 45°, which provides additional protection against exceeding the minimum bend radius. The 45° angle also protects the patch cord/jack connection from being damaged from office furniture. AFP plates include 2 smooth locations for adhesive labels or can be fitted with optional snap in clear label covers and paper inserts.



Application

Areas with Capacity Bend Radius restrictions

General

Color	Electric Ivory
Construction	Molded
Construction Material - Main	High-Impact Thermoplastic (UL 94V-0)
Cutout	NEMA 1-Gang
EU RoHS Indicator	Yes
Item Type	Faceplate
Material	High-Impact Thermoplastic (UL 94V-0)
Material - Mounting Hardware	Screw
Number Of Ports	4
Number of Gang(s)	1-Gang
Orientation	Vertical
Size	Standard
UPC	662620805573

Dimensions

Display Size	4-Port
--------------	--------

Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none">RoHS CompliantUL and cUL Listed 1863
----------------------	-----------------------------------------------------------------------------------------------

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Warranty - Industrial & Commercial Products](#)

Related Products

- [AFP14G - Single-Gang Keystone Wallplate, Angled, 4-Port, Gray](#)
- [AFP14 - Single-Gang Keystone Wallplate, Angled, 4-Port, Light Almond/Office White](#)
- [AFP14W - Single-Gang Keystone Wallplate, Angled, 4-Port, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-AFP14E-SPEC-EN | REV 5/2023