

EdgeConnect™ Series, Duplex Receptacle,
Commerical Grade, Weather Resistant,
Tamper Resistant, 2-Pole 3-Wire, 20A 125V, 5-
20R, Screwless Terminal, Light Almond

By Hubbell Wiring Device-Kellems
Catalog # [BR15STLAWRTR](#)

Straight Blade Devices, EdgeConnect™ , Duplex Receptacle,
Commercial Grade, Weather Resistant, Tamper Resistant, 2-Pole 3-Wire,
20A 125V, 5-20R, Screwless Terminal, Light Almond

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Triple and Double Wipe Contacts
- Easy access split circuit tab

Specifications

Nema Rating	5-15R
Industry Standard(s)	• UL Listed to UL498 File No. E2186 • Certified to CSA 22.2 • No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant • UL 94 V-2

Conductor

Number Of Poles	2-Pole
Number Of Wires	3-Wire
Wire Size	#14 (Solid and Stranded) - #10 (Stranded) Copper Wire Only

Current

Interrupt Rating	Certified for current interrupting at full rated current A
Voltage Rating	125 V
Dielectric Strength	Withstands 2,000V minimum
Current / Amperage Rating	15 A

Dimensions

Weight	0.3 lb.
Size	3.28x1.58x1.38

General

Color	Light Almond
Style	Smooth Face
Listings	Terminals Identified in Accordance with UL 498 and CSA 783585729725
UPC	783585729725
Type	Weather Resistant & Tamper-Resistant
Item Type	Receptacle
Material	Thermoplastic/C
Series	EdgeConnect™ Series

Logistics

Pallet Quantity	3300
Carton Quantity	10

Operational

Temperature Rating	• Maximum continuous 75°C • minimum -40°C (w/o impact)
--------------------	--

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)

