

EdgeConnect™, Duplex Receptacle,
Commerical Grade, Weather
Resistant, Tamper Resistant, 2-Pole
3-Wire, 20A 125V, 5-20R, Screwless
Terminal, White

By Hubbell Wiring Device-Kellems
Catalog # [BR15STWWRTR](#)

Straight Blade Devices, EdgeConnect™ , Duplex Receptacle,
Commercial Grade, Weather Resistant, Tamper Resistant, 2-Pole
3-Wire, 20A 125V, 5-20R, Screwless Terminal, White

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Triple and Double Wipe Contacts
- Easy access split circuit tab

General

| | |
|--------------------|--|
| Catalog Number | BR15STWWRTR |
| Color | White |
| Item Type | Receptacle |
| Listings | Terminals Identified in Accordance with UL 498 and CSA |
| Material | Thermoplastic/C |
| Number Of Poles | 2-Pole |
| Series | EdgeConnect™ |
| Size | 3.28x1.58x1.38 |
| Style | Smooth Face |
| Temperature Rating | Maximum continuous 75°C; minimum -40°C (w/o impact) |
| Type | Weather Resistant & Tamper- Resistant |
| UPC | 783585729756 |

Electrical Ratings

| | |
|---------------------------|--|
| Current / Amperage Rating | 15 A |
| Dielectric Strength | Withstands 2,000V minimum |
| Interrupt Rating | Certified for current interrupting at full rated current A |



| | |
|----------------|-------|
| Voltage Rating | 125 V |
|----------------|-------|

Conductor Related

| | |
|-----------------|---|
| Number Of Wires | 3-Wire |
| Wire Size | #14 (Solid and Stranded) - #10 (Stranded) Copper Wire Only |

Certifications And Compliance

| | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">• UL Listed to UL498 File No. E2186• Certified to CSA 22.2• No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant• UL 94 V-2 |
| Nema Rating | 5-15R |

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog Page - WDK A-22 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD3029](#)
- [Literature - EdgeConnect™ Technology FAQ](#)
- [Literature - EdgeConnect™ Technology](#)
- [Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
- [Sales Drawings - M-14698](#)
- [Specifications - BR15STWWRTR](#)
- [Warranty - Industrial & Commercial Products](#)