

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 16/20 A 220-240 VAC, 2-POLE 3-WIRE, Blue, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [C320C6WA](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 16/20 A 220-240 VAC, 2-POLE 3-WIRE, Blue, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- External strain relief
- Glandless water ingress protection

Application

High Ampacity Connections

General

Catalog Number	C320C6WA
Color	Blue
Number Of Poles	2-POLE
Series	Hubbell-PRO
Style	Standard Service
Type	Watertight Connector Body
UPC	783585640952

Electrical Ratings

Current / Amperage Rating	16/20 A
Voltage Rating Description	220-240 VAC

Conductor Related

Number Of Wires	3-WIRE
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14032_ACAD](#)
- [Installation Manuals - PD2878_PD2908](#)
- [Literature - Hubbell PRO Pin & Sleeve Brochure](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - M14032](#)
- [Specifications - WIRING_C320C6WA_spec](#)
- [Warranty - Industrial & Commercial Products](#)

