

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 60 A 125 VAC, 2-POLE 3-WIRE, Yellow, Splash Proof

By Hubbell Wiring Device-Kellems  
Catalog # [C360AR4SA](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 60 A 125 VAC, 2-POLE 3-WIRE, Yellow, Splash Proof

Features

- IP44 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- Color coded housings provide quick identification of mating devices

Application

High Ampacity Connections

General

Catalog Number	C360AR4SA
Color	Yellow
Number Of Poles	2-POLE
Series	Hubbell-PRO
Style	Standard Service
Type	Splash Proof Angled Receptacle
UPC	783585678801



Electrical Ratings

Current / Amperage Rating	60 A
Voltage Rating Description	125 VAC

Conductor Related

Number Of Wires	3-WIRE
-----------------	--------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14042\\_ACAD](#)
- [Installation Manuals - PD2879](#)
- [Literature - Hubbell PRO Pin & Sleeve Brochure](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - M14042](#)
- [Specifications - WIRING\\_C360AR4SA\\_spec](#)
- [Warranty - Industrial & Commercial Products](#)

