

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 60 A 125 VAC, 2-POLE 3-WIRE, Yellow, Watertight

By Hubbell Wiring Device-Kellems
Catalog # C360C4WLT100

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 60 A 125 VAC, 2-POLE 3-WIRE, Yellow, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- Integral 1" NPT conduit threading
- Glandless water ingress protection

General

| | |
|-----------------|---------------------------------------|
| Catalog Number | C360C4WLT100 |
| Color | Yellow |
| Number Of Poles | 2-Pole |
| Series | Hubbell-PRO |
| Style | Standard Service |
| Type | Watertight Liquidtight Connector Body |



UPC 783585763903

Electrical Ratings

| | |
|----------------------------|---------|
| Current / Amperage Rating | 60 A |
| Voltage Rating Description | 125 VAC |

Conductor Related

| | |
|-----------------|--------|
| Number Of Wires | 3-Wire |
|-----------------|--------|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

Product Assets

[Sales Drawings - Sales Drawing M-14501](#)
[Specifications - C360C4WLT100](#)
[Warranty - Industrial & Commercial Products](#)