

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 60/63 A 125/250 VAC, 3-POLE 4-WIRE, Blue, Splash Proof

By Hubbell Wiring Device-Kellems
Catalog # [C460AR9SA](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 60/63 A 125/250 VAC, 3-POLE 4-WIRE, Blue, Splash Proof

Features

- IP44 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- Color coded housings provide quick identification of mating devices

Application

High Ampacity Connections

General

Catalog Number	C460AR9SA
Color	Blue
Number Of Poles	3-POLE
Series	Hubbell-PRO
Style	Standard Service
Type	Splash Proof Angled Receptacle
UPC	783585679181



Electrical Ratings

Current / Amperage Rating	60/63 A
Voltage Rating Description	125/250 VAC

Conductor Related

Number Of Wires	4-WIRE
-----------------	--------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14042_ACAD](#)
- [Installation Manuals - PD2879](#)
- [Literature - Hubbell PRO Pin & Sleeve Brochure](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - M14042](#)
- [Specifications - WIRING_C460AR9SA_spec](#)
- [Warranty - Industrial & Commercial Products](#)