

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 30 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight

By Hubbell Wiring Device-Kellems  
Catalog # [C530AR7WA](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 30 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- UL approved screwless terminations
- Color coded housings provide quick identification of mating devices

Application

High Ampacity Connections

General

Catalog Number	C530AR7WA
Color	Red
Number Of Poles	4-POLE
Series	Hubbell-PRO
Style	Standard Service
Type	Watertight Angled Receptacle
UPC	783585675091



Electrical Ratings

Current / Amperage Rating	30 A
Voltage Rating Description	277/480 VAC

Conductor Related

Number Of Wires	5-WIRE
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14043\\_ACAD](#)
- [Installation Manuals - PD2879](#)
- [Literature - Hubbell PRO Pin & Sleeve Brochure](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - M14043](#)
- [Specifications - WIRING\\_C530AR7WA\\_spec](#)
- [Warranty - Industrial & Commercial Products](#)