

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 30 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [C530C7WLT34](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 30 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- UL approved screwless terminations
- Glandless water ingress protection
- Integral 3/4" liquidtight conduit threading

General

Catalog Number	C530C7WLT34
Color	Red
Number Of Poles	4-POLE
Series	Hubbell-PRO
Style	Standard Service
Type	Watertight Liquidtight Connector Body
UPC	783585714134



Electrical Ratings

Current / Amperage Rating	30 A
Voltage Rating Description	277/480 VAC

Conductor Related

Number Of Wires	5-Wire
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-20 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Sales Drawings - Sales Drawing M-14499](#)
- [Specifications - C530C7WLT34](#)
- [Warranty - Industrial & Commercial Products](#)