

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Male, Plug, 30/32 A 200-415 VAC, 4-POLE 5-WIRE, Red, Splash Proof

By Hubbell Wiring Device-Kellems
Catalog # [C530P6SA](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Male, Plug, 30/32 A 200-415 VAC, 4-POLE 5-WIRE, Red, Splash Proof

Features

- IP44 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- UL approved screwless terminations
- Glandless water ingress protection

Application

High Ampacity Connections

General

Catalog Number	C530P6SA
Color	Red
Number Of Poles	4-POLE
Series	Hubbell-PRO
Style	Standard Service
Type	Splash Proof Plug
UPC	783585678221

Electrical Ratings

Current / Amperage Rating	30/32 A
---------------------------	---------



Voltage Rating Description	200-415 VAC
----------------------------	-------------

Conductor Related

Number Of Wires	5-WIRE
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-19 Catalog Page](#)
- [Catalog Page - WDK G-20 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14031_ACAD](#)
- [Installation Manuals - PD2878_PD2908](#)
- [Literature - IHubbell-PRO EC pin & sleeve devices](#)
- [Literature - Hubbell PRO Pin & Sleeve Brochure](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - M14031](#)
- [Specifications - WIRING_C530P6SA_spec](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Hubbell PRO Liquidtight IEC Pin & Sleeve](#)