

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 30 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight

By Hubbell Wiring Device-Kellems
Catalog # [C530R7WA](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 30 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- UL approved screwless terminations
- Color coded housings provide quick identification of mating devices

Application

High Ampacity Connections

General

Catalog Number	C530R7WA
Color	Red
Number Of Poles	4-POLE
Series	Hubbell-PRO
Style	Standard Service
Type	Watertight Receptacle
UPC	783585675053

Electrical Ratings

Current / Amperage Rating	30 A
Voltage Rating Description	277/480 VAC

Conductor Related

Number Of Wires	5-WIRE
-----------------	--------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK G-17 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14034_ACAD](#)
- [Installation Manuals - PD2879](#)
- [Literature - Hubbell PRO Pin & Sleeve Brochure](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - M14034](#)
- [Specifications - WIRING_C530R7WA_spec](#)
- [Warranty - Industrial & Commercial Products](#)

