

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 60/63 A 200-415 VAC, 4-POLE 5-WIRE, Red, Splash Proof

By Hubbell Wiring Device-Kellems
Catalog # [C560C6SA](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 60/63 A 200-415 VAC, 4-POLE 5-WIRE, Red, Splash Proof

Features

- IP44 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- External strain relief
- Glandless water ingress protection

Application

High Ampacity Connections

General

Catalog Number	C560C6SA
Color	Red
Number Of Poles	4-POLE
Series	Hubbell-PRO
Style	Standard Service
Type	Splash Proof Connector
UPC	783585679211

Electrical Ratings

Current / Amperage Rating	60/63 A
Voltage Rating Description	200-415 VAC

Conductor Related

Number Of Wires	5-WIRE
-----------------	--------

Logistics

Carton Quantity	5
Pallet Quantity	375

Product Assets

- [Catalog Page - WDK G-19 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14033_ACAD](#)
- [Installation Manuals - PD2878_PD2908](#)
- [Literature - Hubbell PRO Pin & Sleeve Brochure](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - IEC Pin & Sleeve Devices](#)
- [Sales Drawings - M14033](#)
- [Specifications - WIRING_C560C6SA_spec](#)
- [Warranty - Industrial & Commercial Products](#)

