



Wiring Device-Kellems

C560C7WLT34

By Hubbell Wiring Device-Kellems
Catalog # [C560C7WLT34](#)



Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Connector Body, 60 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight

Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- External strain relief
- Glandless water ingress protection

General

| | |
|-----------------|---------------------------------------|
| Color | Red |
| Number Of Poles | 4-POLE |
| Series | Hubbell-PRO |
| Style | Standard Device |
| Type | Watertight Liquidtight Connector Body |
| UPC | 783585714233 |

Electrical Ratings

| | |
|----------------------------|-------------|
| Current / Amperage Rating | 60 A |
| Voltage Rating Description | 277/480 VAC |

Conductor Related

| | |
|-----------------|--------|
| Number Of Wires | 5-WIRE |
|-----------------|--------|

Logistics

| | |
|-----------------|---|
| Carton Quantity | 5 |
|-----------------|---|

Product Assets

[Sales Drawings - WDK_M-14501_SalesDrawing](#)

Related Products

- [FW60100 - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A and 100A 1 1/2" NPT Hub, 4 Way Angled, Mounting Screws Included](#)
- [PC3430 - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Male Closure Cap, For 30A 3 and 4-Wire Gray Non-Metallic](#)
- [C560AR7WA - Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Female, Receptacle, 60 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight](#)
- [BB602W - Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Back Box, For 60A 1 1/2" NPT Hub, Angled, Mounting ScrewsIncluded Cast Aluminum](#)
- [C560P7WA - Heavy Duty Products, IEC Pin and Sleeve Devices, Hubbell-PRO, Male, Plug, 60 A 277/480 VAC, 4-POLE 5-WIRE, Red, Watertight](#)



A proud member of the Hubbell Family.