



Wiring Device-Kellems

Switches and Lighting Controls, Daylight Control, Dimming Ballasts, 0-10 Volt

By Hubbell Wiring Device-Kellems
Catalog # [DHADC](#)



Switches and Lighting Controls, Daylight Control, Dimming Ballasts, 0-10 Volt

Features

- 0-10V DC, Single zone continuous automatic dimming control
- Light-sensitivity range of 0-500 foot-candles
- Selectable 3- or 8-second dimming rate

Application

For use with 0-10V DC dimming ballasts.

General

Color	White
Series	Indoor
Style	Photocell
UPC	783585158532

Electrical Ratings

Voltage Rating	10 VDC
Voltage Rating Description	0-10V DC

Product Assets

- [BIM - Lighting_Device-Daylight_Harvesting-Hubbell_Wiring-DH](#)
- [Catalog Page - Wiring E-11 Catalog Page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Installation Manuals - WIRING_DHADC_INSTALLINST](#)
- [Literature - Load Control Application Guide](#)
- [Warranty - HMOSS Occupancy Motion Sensors](#)

Related Products

- [DHT - Switches and Lighting Controls, PhotocellControl, Daylight Tracker](#)
- [DHIP - Switches and Lighting Controls, Daylight Control, Indoor Photocell Control](#)
- [DHOP - Switches and Lighting Controls, Daylight Control, Outdoor Photocell Control](#)
- [DHAP - Switches and Lighting Controls, Daylight Control, Sensor, Atrium Photocell](#)
- [DHCM - Switches and Lighting Controls, Daylight Control, Daylight Photocell Control](#)



A proud member of the Hubbell Family.