

Switches and Lighting Controls, Daylight Control, Indoor Photocell Control

By Hubbell Wiring Device-Kellems

Catalog # [DHIP](#)



Switches and Lighting Controls, Daylight Control, Indoor
Photocell Control

Features

- 24V DC, indoor photocell
- Light-sensitivity range of 5-750 foot-candles

General

Application	For use with DHCM and CU series control units.
Color	White
EU RoHS Indicator	No
Photocell	Yes
Series	Indoor
Style	Photocell
UPC	783585158549

Electrical Ratings

Voltage Rating	24 VDC
Voltage Rating Description	24V DC

Product Assets

[BIM - Lighting_Device-Daylight_Harvesting-Hubbell_Wiring-DH](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - DHIP AutoCAD Drawing](#)
[Sales Drawings - WDK_DHIP_DRAWING_PDF](#)
[Warranty - HMOSS Occupancy Motion Sensors](#)