

# Switches and Lighting Controls, Daylight Control, Outdoor Photocell Control

By Hubbell Wiring Device-Kellems

Catalog # [DHOP](#)



Switches and Lighting Controls, Daylight Control, Outdoor  
Photocell Control

## Features

- 24V DC, outdoor photocell
- Light-sensitivity range of 5-750 foot-candles

## General

Application	For use with DHCM and CU series control units.
Color	White
EU RoHS Indicator	No
Photocell	Yes
Series	Outdoor
Style	Photocell
UPC	783585158556

## Electrical Ratings

Voltage Rating	24 VDC
Voltage Rating Description	24V DC

## Product Assets

[BIM - Lighting\\_Device-Daylight\\_Harvesting-Hubbell\\_Wiring-DH Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - DHOP AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2354\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_DHOP\\_DRAWING\\_PDF](#)  
[Warranty - HMOSS Occupancy Motion Sensors](#)