

EdgeConnect™, Decorator
Receptacle, Commerical Grade,
Weather Resistant, 2-Pole 3-Wire,
15A 125V, 5-15R, Screwless
Terminal, Red

By Hubbell Wiring Device-Kellems
Catalog # [DR20STRWR](#)

Straight Blade Devices, EdgeConnect™ , Decorator Receptacle,
Commercial Grade, Weather Resistant, 2-Pole 3-Wire, 15A 125V,
5-15R, Screwless Terminal, Red

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Triple and Double Wipe Contacts
- Easy access split circuit tab

General

Catalog Number	DR20STRWR
Color	Red
Item Type	Receptacle
Listings	Terminals Identified in Accordance with UL 498 and CSA
Material	Thermoplastic/C
Number Of Poles	2-Pole
Series	EdgeConnect™
Size	3.28x1.58x1.38
Style	Style Line Decorator
Temperature Rating	Maximum continuous 75°C; minimum -40°C (w/o impact)
Type	Weather Resistant
UPC	783585730240

Electrical Ratings

Current / Amperage Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Interrupt Rating	Certified for current interrupting at full rated current A



Voltage Rating	125 V
----------------	-------

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 (Solid and Stranded) - #10 (Stranded) Copper Wire Only

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• UL Listed to UL498 File No. E2186• Certified to CSA 22.2• No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant• UL 94 V-2
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK A-22 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - PD3029](#)
[Literature - EdgeConnect™ Technology FAQ](#)
[Literature - EdgeConnect™ Technology](#)
[Literature - EdgeConnect™ Termination vs Standard Push Wire](#)
[Sales Drawings - M-14699](#)
[Specifications - DR20STRWR](#)
[Warranty - Industrial & Commercial Products](#)