

Switches and Lighting Control,
Decorator Switch Specification
Grade, Rocker Switches, General
Purpose AC, Illuminated Single
Pole, 20A 120/277V AC

By Hubbell Wiring Device-Kellems
Catalog # [DS120ILLA](#)



Switches and Lighting Control, Decorator Switch Specification
Grade, Rocker Switches, General Purpose AC, Illuminated Single
Pole, 20A 120/277V AC, Back and Side Wired, Light Almond

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 20A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - #14 AWG min. - #10 AWG max. solid and stranded copper wire only

General

Catalog Number	DS120ILLA
Color	Light Almond
EU RoHS Indicator	No
Indicator	Light On with Load Off
Indicator(s) Type	Blue LED
Item Type	Single Pole Style Line Illuminated Decorator Switch
Material	Thermoplastic
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Illuminated
Specifications	<ul style="list-style-type: none">• Contacts - Silver Alloy• Contacts - Silver Alloy• Ground Screw - Brass (Green)

Style	Single Pole
Type	Rocker/Decorator
UPC	783585169941

Dimensions

Dimensions	4.28 in x 1.43 in x 1.54 in
Height	1.54 in
Length	4.28 in
Weight	0.2 lb
Width	1.43 in

Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC

Conductor Related

Wire Size	#14 AWG to #10 AWG
-----------	--------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK D-16 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2444_INSTALLINST](#)

[Sales Drawings - WDK_DS120I_DRAWING_PDF](#)
[Specifications - DS120ILLA](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-DS120ILLA-SPEC-EN | REV 3/2025