



Low voltage switch, 0-10V dimmer, current sinking capacity, 30mA

By Hubbell Wiring Device-Kellems
Catalog # [DSC010BK](#)

Low voltage switch, 0-10V dimmer, current sinking capacity, 1
Latching, 1 Momentary, 4 button, 30mA

Features

- 4-button switch
- Bi-level lighting & partial ON operation
- Pilot Light
- Single Gang Design

General

Color Black
UPC 783585565040

Logistics

Carton Quantity 10



Oh No!
IMAGE COMING SOON

Product Assets

[Warranty - HMOSS Occupancy Motion Sensors](#)

Related Products

[AU2000I1 - Wall Switch, Occupancy or Vacancy, Ultrasonic, 800W Incandescent, 1000W Fluorescent @ 120V AC, 1800W Fluorescent @ 277VAC, 120/277V AC](#)

[DSL010I - Switches and Lighting Control, DimmingSwitch, Low Voltage, Latching, 0-10V DC, Ivory](#)

[DSC010LA - Switches and Lighting Control, DimmingSwitch, Low Voltage, Latching Combo, 0-10V DC, Light Almond](#)

[CU300HD - Switches and Lighting Control, Occupancy Sensor, Control Unit, 120/277V AC, Heavy Duty Relay, Latching](#)

[DSC010W - Switches and Lighting Control, DimmingSwitch, Low Voltage, Latching Combo, 0-10V DC, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-DSC010BK-SPEC-EN | REV 5/2023