



Pedestal, 2-Gang, Almond

By Hubbell Wiring Device-Kellems
Catalog # [FR280ALA](#)



Fire-Rated Poke-Through Pedestal, Double

Features

- 1-4 hour fire rating (1-3 hour for steel floor units and concrete topping, D900 Series Design)
- For 2 ¼ in. to 7 in. floor thickness
- Approved for use in the City of Chicago

Application

Through Floor Delivery

General

Color	Almond
Construction	Fabricated
Construction Material - Main	280 Meunt
EU RoHS Indicator	No
Finish Type	Aluminum
Item Type	2-Gang Above Floor Service Fittings
Knockouts	None
Material	Aluminum
Material - Mounting Hardware	On PT27A Through Floor Fitting
Mounting Hardware	Included
Mounting Type	On PT27A or PT7XC Through Floor Fitting
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	Electrical - Service Pedestal Construction - Heavy gauge galvanized steel frame with aluminum housing and face plates
Size	Standard Sized Product
Style	Pedestals
Sub Brand	Accessories
Type	Above Floor Service Fittings
UPC	783585396231

Dimensions

Display Size Standard Sized Product

Conductor Related

Cable Entry Direct into Device

Certifications and Compliance

Industry Standard(s) UL 514A

Logistics

Carton Quantity 5

Product Assets

[Catalog Page - Wiring Q-34 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - FR280ALA AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1901_INSTALLINST](#)
[Sales Drawings - WDK_FR280A_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[SS2309BALA - Pedestal Face Plate, Blank, Aluminum](#)
[SS2309FALA - Pedestal Face Plate, 3/4" KO, Aluminum](#)
[PT27A - 2" Though Floor Fitting](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-FR280ALA-SPEC-EN | REV 5/2023